

CYBEX™ SC800/SC900 SECURE DESKTOP HDMI KVM SWITCHES



Superior security and control at the desktop
NIAP PP 3.0 Compliant, Common Criteria Tested and Certified

OVERVIEW

KEY FEATURES

- Advanced isolation between computers and shared peripherals
- Support for HDMI in single and dual head models supporting resolutions up to UHD 4K

BENEFITS

- Compliant to NIAP Protection Profile for Peripheral Sharing Switches, version 3.0
- Unidirectional Optical Data Diodes assure USB peripheral isolation enabling data flow from devices to host only
- Always-on active anti-tampering system
- Dedicated Peripheral Port (DPP) for connecting authentication devices such as biometric readers and smart card readers
- Hardware-based peripheral isolation loads all firmware on ROM with no keyboard buffering or memory
- Full USB device filtering to assure support for keyboard and mouse only
- Mouse and keyboard switching via emulation assures zero delay in switching them between connected sources



SPECIFICATIONS

MODEL NUMBER	SC820H/SC920H	SC840H/SC845H/SC940H/SC945H
System Connections	2	4
System Support	HDMI 1.4	
Display Connections	Single Head SC8xx, Dual Head SC9xx	
Display Support	HDMI 1.4	
Max Resolution	UHD 4K - 3840 x 2160 @30Hz	
CONNECTIONS		
Console Peripherals	USB Type - A	
Computer Peripherals	USB Type - B	
Dedicated Peripheral Port	0	1 (SC845H/SC945H)
Audio Input/Output	1 x 3.5 mm stereo female	
MECHANICAL		
Enclosure	Steel with plastic front panel	
Dimensions	7 x 2.4 x 1.7 (178 x 61 x 43) SC8XX	13.7 x 5 x 1.7 (348 x 127 x 43) SC8XX
W x D x H in / (mm)	7 x 2.4 x 2.2 (178 x 61 x 56) SC9XX	13.7 x 5 x 2.2 (348 x 127 x 56) SC9XX
Weight lbs / (kg)	1.0 (0.5) SC8XX / 1.5 (0.7) SC9XX	3.0 (1.5) SC8XX / 3.7 (1.9) SC9XX
POWER		
Power Requirements	12V DC 1.5A Power Adapter	35W Max Internal
AC Input Voltage	100 to 240V AC	
ENVIRONMENTAL		
Operating Temperature	32° to 104°F; 0° to 40°C	
Storage Temperature	-4° to 140°F; -20° to 60°C	
Humidity	0-80% RH, non-condensing	
Certifications	CE, RCM, FCC class B, VCCI, TUV US, TUV Canada	
Warranty	3 Years	



SC845H rear panel

Ordering Details

MODEL NUMBER	CABLE OPTIONS-LENGTH	CABLE DESCRIPTION
SC820H/SC840H	CBL0110 - 6 ft. , CBL0111 - 10 ft.	CABLE ASSY, 1-HDMI/1-USB/1-AUDIO
	CBL0162 - 6 ft.	CABLE ASSY, 1-HDMI/1-USB/1-DVI-D/1-AUDIO
SC845H	CBL0112 - 6 ft. , CBL0113 - 10 ft.	CABLE ASSY, 1-HDMI/2-USB/1-AUDIO
	CBL0164 - 6 ft.	CABLE ASSY, 1-HDMI/2-USB/1-DVI-D/1-AUDIO
SC920H/SC940H	CBL0114 - 6 ft. , CBL0115 - 10 ft.	CABLE ASSY, 2-HDMI/1-USB/1-AUDIO
	CBL0166 - 6 ft.	CABLE ASSY, 2-HDMI/1-USB/2-DVI-D/1-AUDIO
SC945H	CBL0116 - 6 ft. , CBL0117 - 10 ft.	CABLE ASSY, 2-HDMI/2-USB/1-AUDIO
	CBL0168 - 6 ft.	CABLE ASSY, 2-HDMI/2-USB/2-DVI-D/1-AUDIO

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2018 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.