



FRONT VIEW



REAR VIEW



SIDE VIEW

- ① OFF/ENTER BUTTON
- ② SELECT BUTTON
- ③ ON/MUTE BUTTON
- ④ INPUT POWER CORD: NEMA 5-15P WITH 10 FOOT ATTACHED CORD
- ⑤ 13A INPUT CIRCUIT BREAKER
- ⑥ USB PORT
- ⑦ EPO CONNECTOR
- ⑧ RJ-45 DATA LINE CONNECTORS
- ⑨ INTELLISLOT PORT. NETWORK COMMUNICATIONS CARD OPTIONAL
- ⑩ OUTPUT RECEPTACLES: 3 NEMA 5-15R ALWAYS ON
- ⑪ OUTPUT RECEPTACLES: 2 NEMA 5-15R PROGRAMMABLE OUTPUT GROUP

NOTES:

1. UNIT DIMENSIONS: 5.7" x 14.8" x 8.7" (145mm) x (376mm) x (220mm)
2. UNIT WEIGHT: 26.0LBS (11.8KG)
3. SHIPPING DIMENSIONS: 9.1" x 17.7" x 12.8" (230mm) x (450mm) x (325mm)
4. SHIPPING WEIGHT: 29.1LBS (13.2KG)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100.0mm) - FRONT/REAR/SIDE
6. ALL SITE WIRING IS TO BE IN COMPLIANCE WITH NATIONAL AND LOCAL ELECTRIC CODES
7. UNIT INPUT: 100~125 VAC, 60/50HZ, 10A
8. UNIT OUTPUT: 100/110/115/120/125VAC, 60/50HZ,
 1100VA/990W, 8.8A, @125VAC INPUT OR
 1100VA/990W, 9.2A, @120VAC INPUT OR
 1100VA/990W, 9.6A, @115VAC INPUT OR
 935VA/842W, 8.5A, @110VAC INPUT OR
 935VA/842W, 9.4A, @100VAC INPUT

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

PSI5-1100MT120

DWG. NO. PSI5-1100MT120	DATE 10-14-19	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
----------------------------	------------------	-------------	---

