



**REAR VIEW**

**SIDE VIEW**

**FRONT VIEW**



AGENCY COMPLIANCE:  
UL & c-UL Listed 60950  
RoHS Compliant  
FCC Part 15 Class A Conformance

ENVIRONMENTAL RATING:  
Maximum Operating Temperature: 60C / 140F

NOTES  
UNIT DIMENSIONS: 66.25in x 2.0in x 2.6in / 1683mm x 51mm x 66mm  
SHIPPED WEIGHT: 20lbs (9.07kg)  
SHIPPING DIMENSIONS: 72in x 9in x 7in / 1829mm x 223mm x 159mm  
Toolless Mounting Hardware 61.25in / 1556mm and 64.75in / 1645mm, and 7938 Vertical Mounting Bracket Kit

**OUTPUT POWER**

| CIRCUIT | PHASE | RECEPTACLE TYPE<br>(QUANTITY) | VOLTAGE (V) | MAX. CONTINUOUS AMPS (A) |             |
|---------|-------|-------------------------------|-------------|--------------------------|-------------|
|         |       |                               |             | PER RECEPTACLE           | PER CIRCUIT |
| 1       | L1    | 12XNEMA 5-20R                 | 100-120     | 16                       | 16          |
| 2       | L1    | 12XNEMA 5-20R                 | 100-120     | 16                       | 16          |

**INPUT POWER**

| INPUT CORD | INPUT PLUG  | WIRE COUNT | FREQUENCY<br>(Hz) | VOLTAGE<br>(V) | RATED AMPS<br>(A) | MAX. CONT.<br>AMPS (A) |
|------------|-------------|------------|-------------------|----------------|-------------------|------------------------|
| 10 FT      | NEMA L5-30P | 1/N/PE     | 50/60 Hz          | 100-120V       | 30                | 24                     |

| METERING PARAMETER | MEASUREMENT ACCURACY                                 |
|--------------------|--|
| VOLTAGE            | ±1%  |
| CURRENT            | ±1% - Input Current<br>±2% - Circuit/Breaker Current |

|                         |  |   |  |                      |  |                      |  |   |  |
|-------------------------|--|---|--|----------------------|--|----------------------|--|---|--|
| <p>Dimensions in mm</p> |  | Allgemeintoleranzen<br>General tolerances |  | Oberfläche<br>Finish |  | Werkstoff / Material |  | Gewicht:<br>Weight: -                                   |  |
|                         |  | -   |  | -                    |  | -                    |  | -   |  |
| Rev.                    |  | Change                                    |  | Date                 |  | Name                 |  | Bezeichnung / Description                               |  |
| -                       |  | -   |  | 21/06/18             |  | SW                   |  | Switched, Unit Level, Vertical, 30A, 120V,<br>(24)5-20R |  |
| -                       |  | -   |  | -                    |  | -                    |  | Zeichnungs-Nr. / Drawing no.                            |  |
| -                       |  | -   |  | -                    |  | -                    |  | <b>VP8932</b>   |  |
| -                       |  | -   |  | -                    |  | -                    |  | Verwendet in / Used in                                  |  |
| -                       |  | -   |  | -                    |  | -                    |  | Blatt/Sheet<br>1/1                                      |  |



Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.