

# Vertiv™ NetSure™ Inverter System



Stand-Alone AC Power System

## Benefits

- Leverage existing DC power infrastructure with easy to add subrack.
- Minimize energy consumption with 95.2% peak efficiency in normal AC-AC mode.
- Maximize site availability thanks to zero transfer time from grid to battery.
- Manage the inverter system locally or remotely through the NetSure™ Control Unit (NCU).

## Service

- Get the job done right by leveraging a professional team.
- Rest assured your inverter system is installed properly and configured optimally.
- Reduce risk of long-term damage and protect your warranty.
- Ensure system settings are optimized and meet your standards.

*The stand-alone Vertiv™ NetSure™ Inverter System allows you to support AC loads from existing DC power systems and batteries.*

### Improve reliability and save space

The stand-alone Vertiv™ NetSure™ Inverter system delivers outstanding reliability, modularity and scalability. With market leading inverter module density, the system supports your AC loads in a compact footprint. Rectifiers and inverters are connected to the same battery bank which not only facilitates zero second transfer time should commercial AC fail, but also saves space and reduces financial investment.

### Grow as you go

System sizes range from 5 kVA to 24 kVA and accommodate modular 1 kVA/1 kW AC inverters that allow you to add inverters as your loads increase. They are available in 19" wide with bulk outputs or 23" wide with NEMA outlets. NetSure inverter systems can be used in conjunction with any brand or vintage of DC power system that has sufficient capacity to support the additional inverter load.

While primarily designed for field installation with an existing DC power system, these systems can also be ordered from the factory mounted in a variety of relay racks with no cabling.

### Minimize energy loss

The Vertiv™ NetSure™ Inverter Series is designed for efficient operation at any load condition. All models are supported by high-efficiency Vertiv™ eSure™ inverters that deliver up to 95.2% efficiency across a wide operating range. Powering your AC loads with eSure technology helps keep energy loss to a minimum and ensures your network is supported by an extremely reliable backup system.



## Technical Specifications

	5 kVA Bulk Output	6 kVA Bulk Output	10 kVA Bulk Output	12 kVA Bulk Output	15 kVA Bulk Output	20 kVA Bulk Output
	584130100 List 01	584130100 List 01E	584130100 List 03	584130100 List 03E	584130100 List 05	584130100 List 05E
<b>AC Input</b>						
Voltage, Nominal	100 VAC to 125 VAC	100 VAC to 125 VAC	100 VAC to 125 VAC	100 VAC to 125 VAC	-	-
Voltage Range	96 VAC to 140 VAC	96 VAC to 140 VAC	96 VAC to 140 VAC	96 VAC to 140 VAC	-	-
Single or Three-Phase	Single Phase	Single Phase	Single Phase	Single Phase	-	-
Frequency	50 Hz or 60 Hz	50 Hz or 60 Hz	50 Hz or 60 Hz	50 Hz or 60 Hz	-	-
Maximum Current	60 A	72A	120 A	144 A	-	-
Power Factor	>0.99 @ 100% linear load	>0.99 @ 100% linear load	>0.99 @ 100% linear load	>0.99 @ 100% linear load	-	-
Total Harmonic Distortion	< 5% @ 100% linear load	< 5% @ 100% linear load	< 5% @ 100% linear load	< 5% @ 100% linear load	-	-
<b>DC Input</b>						
Voltage, Nominal	40 to 58.5 VDC, 48 VDC (nominal)					
Voltage Range	50 VDC to 58.5 VDC					
Maximum Current	115 A	138 A	230 A	276 A	345 A	460 A
<b>AC Output</b>						
Voltage, Nominal	120 VAC					
Frequency	50 Hz or 60 Hz					
Maximum Power	5 kVA/ 5kW	6 kVA/6 kW	10 kVA/10 kW	12 kVA/12 kW	15 kVA/15 kW	20 kVA/20 kW
Maximum Current	42 A	50.4 A	84.5 A	100.8 A	126 A	168 A
Peak Efficiency	95.2% AC/AC, 92% DC/AC					
Temperature Performance	Full power up to +45 °C (+113 °F) at input voltage range of 100 VAC - 125 VAC					
Over Capacity (fault clearing)	105%-125% @40-48V (15 s), 125%-200% (1 s), >200% (120 ms)					
Load Outputs	Bulk Output(s)					
<b>AC Load Distribution</b>						
Circuit Breaker Type	Rocker Switch					
Circuit Breakers	1	1	2	2	4	4
Circuit Breaker Rating	70 A					
<b>Monitoring</b>						
Module Name	M830B					
Local Display	128 x 160 Pixels TFT LCD					
Communication	RS232, RS485, Ethernet, USB (for software upgrades)					
Protocols	IPv4, IPv6, HTTPS, RADIUS User Authentication, SNMPv2, SNMPv3, EEM, SocTpe, Rsoc, Modbus					
Analog Inputs	2 battery currents, 1 load current, 1 bus voltage, 2 battery voltages, 2 temperatures, fuel level sensor and much more with additional interface boards					
Digital Inputs	1 input for status of surge protective device auxiliary contacts, 12 load fuses, 6 battery fuses, bi-stable contactor status					
Outputs	3 LVDs, (2) bi-stable and (1) mono-stable					
Security	HTTPS, SNMPv3 encryption and RADIUS User Authentication					
IB2 Interface Board	8 relay outputs, 8 digital inputs, 2 temperatures					
IB4 Interface Board	Additional Ethernet port					
SMTEMP Board	Optional temperature concentrator with up to 8 temperature sensors					
<b>Environmental</b>						
Operating Temperature	-20°C to +65°C/-4° F to +149° F (full power up to +45°C/113° F)					
Storage Temperature	-40°C to 70°C / -40°F to +158°F					
Relative Humidity	<95%					
Altitude	3000 m, 10000 ft. (2000 m, 6562 ft. at full power)					
<b>Physical Characteristics</b>						
Color	Grey					
Height	3.5" /88.9 mm	5.25"/133.4 mm	7"/177.8 mm	8.75"/222.3 mm	12.25"/311.2 mm	14"/355.6 mm
Width	17.5"/444.5 mm	17.5"/444.5 mm	17.5"/444.5 mm	17.5"/444.5 mm	17.5"/444.5 mm	17.5"/444.5 mm
Depth	16.6"/421.6 mm	16.6"/421.6 mm	16.6"/421.6 mm	17.4"/442.0 mm	17.4"/442.0 mm	17.4"/442.0 mm
Weight (Approximate)	21 lbs	32 lbs	32 lbs	54 lbs	53 lbs	63 lbs
Module Slots	5	10	10	15	15	20
Mounting Width	19"					
Access	Rear Cabling					
<b>Standards Compliance</b>						
Safety	UL 1778; CUL, CSA C22.2 NO.107.3					
EMC	IEC/EN 61000-4-2; IEC/EN 61000-4-5; GR-1089; FCC Part 15 (CFR47); Conducted Emission: Class A; Radiated Emission: Class B					
Ingress Protection	IP20					
<b>1 kVA/1 kW Inverter Module</b>						
Part Number	11120-100					
<b>Warranty</b>						
Standard Warranty	1 Year Warranty					

	6 kVA Outlet Output	6 kVA Outlet Output	12 kVA Outlet Output	12 kVA Outlet Output	18 kVA Outlet Output	24 kVA Outlet Output
	584130100 List 02	584130100 List 02E	584130100 List 04	584130100 List 04E	584130100 List 06	584130100 List 06E
<b>AC and DC Input</b>						
Voltage, Nominal	100 VAC to 125 VAC					
Voltage Range	96 VAC to 140 VAC					
Single or Three-Phase	Single Phase					
Frequency	50 Hz or 60 Hz					
Maximum Current	72 A	72 A	144 A	144 A	216 A	288 A
Power Factor	>0.99 @ 100% linear load					
Total Harmonic Distortion	< 5% @ 100% linear load					
<b>DC Input</b>						
Voltage, Nominal	40 to 58.5 VDC, 48 VDC (nominal)					
Voltage Range	50 VDC to 58.5 VDC					
Maximum Current	138 A	138 A	276 A	276 A	414 A	552 A
<b>AC Output</b>						
Voltage, Nominal	120 VAC					
Frequency	50 Hz or 60 Hz					
Maximum Power	5.76 kVA/5.76 kW (per NEC breaker de-rating)	5.76 kVA/5.76 kW (per NEC breaker de-rating)	11.5 kVA/11.5 kW (per NEC breaker de-rating)	11.5 kVA/11.5 kW (per NEC breaker de-rating)	18 kVA/18 kW (per NEC breaker de-rating)	23 kVA/23 kW (per NEC breaker de-rating)
Maximum Current	50.4 A	50.4 A	100.8 A	100.8 A	151.2 A	199.2 A
Peak Efficiency	95.2% AC/AC, 92% DC/AC					
Temperature Performance	Full power up to +45 °C (+113 °F) at input voltage range of 100 VAC - 125 VAC					
Over Capacity (fault clearing)	105%-125% @40-48V (15 s), 125%-200% (1 s), >200% (120 ms)					
Load Outputs	NEMA Outlets					
<b>AC Load Distribution</b>						
Circuit Breaker Type	Toggle Switch					
Circuit Breakers	4	4	8	8	16	16
Circuit Breaker Rating	15 A					
<b>Monitoring</b>						
Module Name	M830B					
Local Display	128 x 160 Pixels TFT LCD					
Communication	RS232, RS485, Ethernet, USB (for software upgrades)					
Protocols	IPv4, IPv6, HTTPS, RADIUS User Authentication, SNMPv2, SNMPv3, EEM, SocTpe, Rsoc, Modbus					
Analog Inputs	2 battery currents, 1 load current, 1 bus voltage, 2 battery voltages, 2 temperatures, fuel level sensor and much more with additional interface boards					
Digital Inputs	1 input for status of surge protective device auxiliary contacts, 12 load fuses, 6 battery fuses, bi-stable contactor status					
Outputs	3 LVDs, (2) bi-stable and (1) mono-stable					
Security	HTTPS, SNMPv3 encryption and RADIUS User Authentication					
IB2 Interface Board	8 relay outputs, 8 digital inputs, 2 temperatures					
IB4 Interface Board	Additional Ethernet port					
SMTEMP Board	Optional temperature concentrator with up to 8 temperature sensors					
<b>Environmental</b>						
Operating Temperature	-20°C to +65°C/-4°F to +149°F (full power up to +45°C/113°F)					
Storage Temperature	-40°C to 70°C / -40°F to +158°F					
Relative Humidity	<95%					
Altitude	3000 m, 10000 ft. (2000 m, 6562 ft. at full power)					
<b>Physical Characteristics</b>						
Color	Grey					
Height	3.5"/88.9 mm	5.25"/133.4 mm	7"/177.8 mm	8.75"/222.3 mm	12.25"/311.2 mm	14"/355.6 mm
Width	21.1"/535.9 mm	21.1"/535.9 mm	21.1"/535.9 mm	21.1"/535.9 mm	21.1"/535.9 mm	21.1"/535.9 mm
Depth	16.6"/421.6 mm	16.6"/421.6 mm	16.6"/421.6 mm	18.0"/458.7 mm	18.0"/458.7 mm	18.0"/458.7 mm
Weight (Approximate)	24 lbs	37 lbs	37 lbs	61 lbs	61 lbs	73 lbs
Module Slots	6	12	12	18	18	24
Mounting Width	23"					
Access	Rear Cabling/Front Outlets					
<b>Standards Compliance</b>						
Safety	UL 1778; CUL, CSA C22.2 NO.107.3					
EMC	IEC/EN 61000-4-2; IEC/EN 61000-4-5; GR-1089; FCC Part 15 (CFR47); Conducted Emission: Class A; Radiated Emission: Class B					
Ingress Protection	IP20					
<b>1 kVA/1 kW Inverter Module</b>						
Part Number	11120-100					
<b>Warranty</b>						
Standard Warranty	1 Year Warranty					

## Ordering Information

### 19" Wide Systems with Bulk Distribution Output

58413010001	5 kVA system with 5 inverter slots and one (1) 70A distribution breaker
58413010001E	6 kVA system with 10 inverter slots and one (1) 70A distribution breaker
58413010003	10 kVA system with 10 inverter slots and two (2) 70A distribution breakers
58413010003E	12 kVA system with 15 inverter slots and two (2) 70A distribution breakers
58413010005	15 kVA system with 15 inverter slots and four (4) 70A distribution breakers (DC INPUT ONLY)
58413010005E	20 kVA system with 20 inverter slots and four (4) 70A distribution breakers (DC INPUT ONLY)

### 23" Wide Systems with NEMA Outlet Output

58413010002	6 kVA system with 6 inverter slots and four (4) NEMA outlets
58413010002E	6 kVA system with 12 inverter slots and four (4) NEMA outlets
58413010004	12 kVA system with 12 inverter slots and eight (8) NEMA outlets
58413010004E	12 kVA system with 18 inverter slots and eight (8) NEMA outlets
58413010006	18 kVA system with 18 inverter slots and sixteen (16) NEMA outlets
58413010006E	24 kVA system with 24 inverter slots and sixteen (16) NEMA outlets

### Modules

11120100	1 kVA/1 kW inverter module
SXA1100035/1	Blank inverter module slot cover
1M830BNA10034162	NCU with software for Stand-Alone inverter systems *

\* One required per stand-alone inverter system - does not occupy an inverter slot. If the stand-alone inverter system is being connected to a NetSure DC power system with an NCU, it is recommended that the NCU in the DC power system be a NCU RevB